


**Transport equipment**

# Product data sheet

Article no.: 2421W Table top cart with steel plate trays



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 3 platforms, trays made of steel sheet, with rim 10 mm high, welded oil-tight, powder coated. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 200 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Shelf heights (mm)</b>	270, 585, 900
<b>Total length (mm)</b>	1197
<b>Total width (mm)</b>	609
<b>Total height (mm)</b>	900
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	64
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976424217