

# KERN FOB-A02

Power adapter (EU/UK/US)

# KERN



## Piktogramme

STANDARD



### Category

Brand	KERN
Product category	Balances
Product group	Power adapter

### Approval

CE mark	✓
---------	---

### Construction

Cable length	1,5 m
--------------	-------

### Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply / adapter for countries - included with the delivery	UK

### Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	93×85×62 mm
Net weight approx.	0,35 kg
Gross weight approx.	0,40 kg
Shipping weight	0,38 kg