

KERN FOB-A10

Power adapter (EU/UK/US)

KERN



Piktogramme

STANDARD



Category

Brand	KERN
Product category	Balances
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Cable length	1,5 m
--------------	-------

Power Supply

Input voltage power supply / power [Max]	230 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 100 mA
Plug-in power supply / adapter for countries - included with the delivery	UK

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	73×89×53 mm
Net weight approx.	0,25 kg
Gross weight approx.	0,30 kg
Shipping weight	0,255 kg