

KERN PFB-A02

Power adapter (EU/UK/US)

KERN



Piktogramme

STANDARD



Category

Brand	KERN
Product category	Balances
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Material	plastic
Cable length	1,8 m

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO CH

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	90×55×80 mm
Net weight approx.	0,10 kg
Gross weight approx.	0,15 kg
Shipping weight	0,127 kg