

KERN 308-32

Milligram weights, E1, 2 mg, Wire, Stainless steel polished

KERN



Services (optional)

Article number for DAkkS calibration 962-252

Pictograms

STANDARD



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E1
Product family	308

Measuring System

Conformity assessment possible	✓
Test weight - nominal value	2 mg
Test weight - volume (cm ³)	0,0003
Test weight - volume uncertainty (cm ³)	0,0001
Permissible tolerance according to OIML (+/-)	0,003 mg
Test weight - Density [Min] (OIML)	2300
Test weight - Density [Max] (OIML)	100000
Weight OIML class	E1

Construction

Shape weight	Wire
Dimensions weight (W×D×H)	6×6×2 mm
Material	Stainless steel polished

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	6×6×2 mm
Net weight	0,000002 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg