

KERN 316-04



Individual weight, OIML Class E2, 10 g, Compact form, stainless steel polished (OIML)



Services (optional)

Article number for conformity assessment	952-334
Article number for DAkkS calibration	962-334
Article number for guaranteed plus-deviation	921-334

Pictograms

STANDARD



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	316

Measuring System

Test weight - nominal value	10 g
Test weight - volume (cm ³)	1,25
Test weight - volume uncertainty (cm ³)	0,0156
Permissible tolerance according to OIML (+/-)	0,06 mg
Test weight - Density [Min] (OIML)	7270
Test weight - Density [Max] (OIML)	8890
Weight OIML class	E2

Construction

Shape weight	Compact form
Dimensions (Ø×H)	10×17,3 mm
Material	stainless steel polished (OIML)

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	10×10×17 mm
Net weight	0,01 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg