

# KERN 316-05



Individual weight, OIML Class E2, 20 g, Compact form, stainless steel polished (OIML)



## Services (optional)

Article number for conformity assessment	952-335
Article number for DAkkS calibration	962-335
Article number for guaranteed plus-deviation	921-335

## Pictograms

## STANDARD



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	316

## Measuring System

Test weight - nominal value	20 g
Test weight - volume (cm <sup>3</sup> )	2,5
Test weight - volume uncertainty (cm <sup>3</sup> )	0,0313
Permissible tolerance according to OIML (+/-)	0,08 mg
Test weight - Density [Min] (OIML)	7500
Test weight - Density [Max] (OIML)	8570
Weight OIML class	E2

## Construction

Shape weight	Compact form
Dimensions (Ø×H)	13×20 mm
Material	stainless steel polished (OIML)

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	13×13×20 mm
Net weight	0,02 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg