

# KERN 317-14



Individual weight, OIML Class E2, 10 kg, Knob, stainless steel polished (OIML)



## Services (optional)

Article number for conformity assessment	952-344
Article number for DAkkS calibration	962-344
Article number for guaranteed plus-deviation	921-344

## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	317

## Measuring System

Conformity assessment possible	✓
Test weight - nominal value	10 kg
Test weight - volume (cm <sup>3</sup> )	1250
Test weight - volume uncertainty (cm <sup>3</sup> )	15,625
Permissible tolerance according to OIML (+/-)	16 mg
Test weight - Density [Min] (OIML)	7810
Test weight - Density [Max] (OIML)	8210
Weight OIML class	E2

## Construction

Shape weight	Knob
Dimensions (Ø×H)	100×185 mm
Material	stainless steel polished (OIML)

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	100×100×185 mm
Net weight	10 kg
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg