

KERN 318-39

Milligram weights, E2, 500 mg, Wire, stainless steel polished (OIML)



Services (optional)

| | |
|--|---------|
| Article number for conformity assessment | 952-359 |
| Article number for DAkkS calibration | 962-359 |
| Article number for guaranteed plus-deviation | 921-359 |

Pictograms

STANDARD



Category

| | |
|------------------|-------------------|
| Brand | KERN |
| Product category | Individual weight |
| Product group | OIML E2 |
| Product family | 318 |

Measuring System

| | |
|---|----------|
| Conformity assessment possible | ✓ |
| Test weight - nominal value | 500 mg |
| Test weight - volume (cm ³) | 0,0625 |
| Test weight - volume uncertainty (cm ³) | 0,0013 |
| Permissible tolerance according to OIML (+/-) | 0,025 mg |
| Weight OIML class | E2 |

Construction

| | |
|---------------------------|---------------------------------|
| Shape weight | Wire |
| Dimensions weight (W×D×H) | 15×15×4 mm |
| Material | stainless steel polished (OIML) |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 15×15×4 mm |
| Net weight | 0,0005 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,05 kg |
| Gross weight approx. | 0,05 kg |
| Shipping weight | 0,1 kg |