

KERN 337-141



Individual weight, OIML Class F2, 10 kg, Check weight, stainless steelfine turned (OIML)



Category

| | |
|------------------|-------------------|
| Brand | KERN |
| Product category | Individual weight |
| Product group | OIML F2 |
| Product family | 337 |

Measuring System

| | |
|-----------------------------------------------------|--------|
| Test weight - nominal value | 10 kg |
| Test weight - volume (cm ³) | 1250 |
| Test weight - volume uncertainty (cm ³) | 15,625 |
| Permissible tolerance according to OIML (+/-) | 160 mg |
| Test weight - Density [Min] (OIML) | 7390 |
| Test weight - Density [Max] (OIML) | 10700 |
| Weight OIML class | F2 |

Construction

| | |
|------------------|-----------------------------------|
| Shape weight | Check weight |
| Dimensions (Ø×H) | 136×132 mm |
| Material | stainless steelfine turned (OIML) |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 136×136×132 mm |
| Net weight | 10 kg |
| Shipping method | Parcel service |
| Net weight approx. | 10 kg |
| Gross weight approx. | 10 kg |
| Shipping weight | 10 kg |

Services (optional)

| | |
|----------------------------------------------|---------|
| Article number for DAkkS calibration | 962-444 |
| Article number for guaranteed plus-deviation | 921-444 |

Pictograms

STANDARD

