

# KERN 337-14



Individual weight, OIML Class F2, 10 kg, Knob, stainless steelfine turned (OIML)



## Services (optional)

Article number for DAkkS calibration	962-444
Article number for guaranteed plus-deviation	921-444

## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

## Measuring System

Conformity assessment possible	no
Test weight - nominal value	10 kg
Test weight - volume (cm <sup>3</sup> )	1250
Test weight - volume uncertainty (cm <sup>3</sup> )	15,625
Permissible tolerance according to OIML (+/-)	160 mg
Test weight - Density [Min] (OIML)	6400
Test weight - Density [Max] (OIML)	10700
Weight OIML class	F2

## Construction

Shape weight	Knob
Dimensions (Ø×H)	100×178 mm
Material	stainless steelfine turned (OIML)

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	100×100×178 mm
Net weight	10 kg
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg