

KERN 337-151



Individual weight, OIML Class F2, 20 kg, Check weight, stainless steelfine turned (OIML)



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

Measuring System

Test weight - nominal value	20 kg
Test weight - volume (cm ³)	2500
Test weight - volume uncertainty (cm ³)	31,25
Permissible tolerance according to OIML (+/-)	300 mg
Test weight - Density [Min] (OIML)	7390
Test weight - Density [Max] (OIML)	10700
Weight OIML class	F2

Construction

Shape weight	Check weight
Dimensions (Ø×H)	136×217 mm
Material	stainless steelfine turned (OIML)

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	137×137×217 mm
Net weight	20 kg
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg

Services (optional)

Article number for DAkkS calibration	962-445
Article number for guaranteed plus-deviation	921-445

Pictograms

STANDARD

