

# KERN 337-15



Individual weight, OIML Class F2, 20 kg, Knob, stainless steelfine turned (OIML)



## Services (optional)

Article number for DAkkS calibration	962-445
Article number for guaranteed plus-deviation	921-445

## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

## Measuring System

Conformity assessment possible	no
Test weight - nominal value	20 kg
Test weight - volume (cm <sup>3</sup> )	2500
Test weight - volume uncertainty (cm <sup>3</sup> )	31,25
Permissible tolerance according to OIML (+/-)	300 mg
Test weight - Density [Min] (OIML)	6400
Test weight - Density [Max] (OIML)	10700
Weight OIML class	F2

## Construction

Shape weight	Knob
Dimensions (Ø×H)	128×230 mm
Material	stainless steelfine turned (OIML)

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	128×128×230 mm
Net weight	20 kg
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg