

# KERN 338-07



Milligram weights, F2, 100 mg, Platelet, stainless steel polished (OIML)



## Services (optional)

Article number for conformity assessment	952-457
Article number for DAkkS calibration	962-457
Article number for guaranteed plus-deviation	921-457

## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	338

## Measuring System

Conformity assessment possible	✓
Test weight - nominal value	100 mg
Test weight - volume (cm <sup>3</sup> )	0,0116
Test weight - volume uncertainty (cm <sup>3</sup> )	0,0002
Permissible tolerance according to OIML (+/-)	0,16 mg
Weight OIML class	F2

## Construction

Shape weight	Platelet
Dimensions weight (W×D×H)	8,5×8,5×4 mm
Material	stainless steel polished (OIML)

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	8,5×8,5×4 mm
Net weight	0,0001 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg