

# KERN 366-88

Individual weight, OIML Class M3, 20 kg, Block, cast iron lacquered

# KERN



## Services (optional)

|                                      |         |
|--------------------------------------|---------|
| Article number for DAkkS calibration | 962-645 |
|--------------------------------------|---------|

## Pictograms

### STANDARD



## Category

|                  |                   |
|------------------|-------------------|
| Brand            | KERN              |
| Product category | Individual weight |
| Product group    | OIML M3           |
| Product family   | 366               |

## Measuring System

|   |           |
|---|-----------|
| Conformity assessment possible                      | no        |
| Test weight - nominal value                         | 20 kg     |
| Test weight - volume (cm <sup>3</sup> )             | 2816,9014 |
| Test weight - volume uncertainty (cm <sup>3</sup> ) | 238,048   |
| Permissible tolerance according to OIML (+/-)       | 10 g      |
| Test weight - Density [Min] (OIML)                  | 1500      |
| Weight OIML class                                   | M3        |

## Construction

|                           |                     |
|---------------------------|---------------------|
| Shape weight              | Block               |
| Dimensions weight (W×D×H) | 230×115×139 mm      |
| Material                  | cast iron lacquered |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Readability force [d] (N)    | 1 d            |
| Dimensions packaging (W×D×H) | 230×115×139 mm |
| Net weight                   | 20 kg          |
| Shipping method              | Parcel service |
| Net weight approx.           | 20 kg          |
| Gross weight approx.         | 20 kg          |
| Shipping weight              | 20 kg          |