

KERN 470-902-003

Mains adapter US 120V/60Hz

KERN



Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Material	plastic
----------	---------

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V, 300 mA
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	US

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	65×80×55 mm
Net weight	0,15 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,25 kg
Shipping weight	0,25 kg