

KERN 572-909N

Power adapter (EU/UK/US)

KERN



Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Material	plastic
----------	---------

Power Supply

Input voltage power supply / power [Max]	100 V - 230 V
Input voltage device / power [Max]	12 V, 300 mA
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Environmental conditions

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	95×70×70 mm
Net weight	0,09 kg
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,15 kg
Shipping weight	0,141 kg