KERN AHBA-01



7 hardness comparison plates for Shore A, tolerance up to $\pm\ 2$ HA



Pictograms

STANDARD



Category	
Brand	Sauter
Product categoriy	Measurementtechnology
Product group	Hardness test block

Construction	
Dimension housing (W×D×H)	51×51×7 mm
Dimensions completely mounted (W×D×H)	50×50×7 mm
Material	plastic
Material housing	plastic

Environmental conditions	
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	175×90×60 mm
Net weight	0,16 kg
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,40 kg
Shipping weight	0,38 kg

Services (optional)	
Article number for factory calibration	961-170

1