

# KERN AHBD-01



3 hardness comparison plates for Shore D, tolerance up to  $\pm 2$  HD



## Pictograms

### STANDARD



## Category

Brand	Sauter
Product category	Measurementtechnology
Product group	Hardness test block

## Construction

Dimension housing (W×D×H)	50×50×7 mm
Dimensions completely mounted (W×D×H)	50×50×7 mm
Material	plastic
Material housing	plastic

## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	173×94×61 mm
Net weight	0,02 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,30 kg
Shipping weight	0,3 kg

## Services (optional)

Article number for factory calibration	961-170
--	---------