KERN BFB 600K-1SNM



Weighing bridge with screwed-on weighing plate (IP67) and XXL display device, verification optional



Category	KEDN
Brand	KERN
Product categoriy	Industrial scale
Product group	Floor scale
Product family	BFB
Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	600 kg
Readability [d]	0,2 kg
Resolution	3.000
Linearity	± 0,6 kg
Reproducibility	0,2 kg
Tare range	-600 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	4 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	600 kg (M2)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	1 kg
Loadcell type	ZEMIC H8C 0.5 ton
Load cell connection	4-wire

1

Approval

CE mark

Pattern approval for conformity assessment	1
Accuracy classe	III
Verification scale interval [e]	0,2 kg
Conformity assessment possible	1
ex works	v
Display	
Display type	LCD
Display screen size	165×64 mm
Display backlight	1
Display digit height	52 mm
Languages of the user interface	Symbol language
Construction	
Dimension display device (W×D×H)	250×160×58 mm
Dimensions weighing platform (W×D×H)	1000×1000×85 mm
Material display housing	Plastics
Material weighing plate	steel, lacquered
Material platform	steel, powder-coated
Dimensions weighing surface (W×D)	1000×1000 mm
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	30 m
Material load cell(s)	alloyed steel
Load cells - number	4
Levelling feet adjustable	\checkmark
Wall mount	1
Stand inclinable	\checkmark
Functions	
Number of keys for operation	7
Auto-off interval(s) in mains power	
mode	selectable
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Tare function	manual (single & multi)
Counting function	1
Tolerance weighing	1
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	1
Recipe/summing level	Sum A
Sum memory function	1

KERN BFB 600K-1SNM



Weighing bridge with screwed-on weighing plate (IP67) and XXL display device, verification optional

Underfloor weighing	None
	RS-232 standard Bluetooth BTC (v2.0)
	(optional, factory)
Interfaces	analogue (0 - 10 V)
	(optional, factory)
	analogue (4 - 20 mA)
IP protection display	(optional, factory) no IP protection
IP protection - display IP protection - load cell	IP67
ir protection - load cell	1F07
Counting	
Reference quantity	10, 20, 50, 100, 200
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for	EURO
countries - included with the	UK
delivery	US CH
	EURO
Dlug in nower ourply (adoptor for	AUS
Plug-in power supply / adapter for countries - optional	UK
obuilties optional	US
	CH
Rechargeable battery optional	Rchrg. battery optional (factory)
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb
Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1110×1070×350 mm
Net weight	105 kg

Shipping method	Freight
Net weight approx.	105 kg
Gross weight approx.	130 kg
Shipping weight	130 kg
Services (optional)	
Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

DAkks +3 days

FACTORY

