KERN BFB 6T-3M



Weighing bridge with steel chequer plate weighing plate and XXL display device, verification optional



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Floor scale
Product family	BFB

Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	6000 kg
Readability [d]	2 kg
Resolution	3.000
Linearity	± 2 kg
Reproducibility	2 kg
Tare range	-6000 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	40 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6000 kg (M2)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	2 kg
Loadcell type	ZEMIC H8C 3 ton
Load cell connection	4-wire

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓

Accuracy classe	III
Verification scale interval [e]	2 kg
Conformity assessment possible ex works	1

Display	
Display type	LCD
Display screen size	165×64 mm
Display backlight	✓
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	250×160×58 mm
Dimensions weighing platform (W×D×H)	1500×1500×130 mm
Material display housing	Plastics
Material weighing plate	steel, lacquered
Material platform	steel, powder-coated
Dimensions weighing surface (W×D)	1500×1500 mm
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	30 m
Material load cell(s)	alloyed steel
Load cells - number	4
Levelling feet adjustable	✓
Wall mount	✓
Stand inclinable	✓

Functions	
Number of keys for operation	20
Auto-off interval(s) in mains power mode	5 min 10 min 30 min
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 10 min 30 min
Tare function	manual (single & multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	√
Recipe/summing level	Sum A
Sum memory function	✓
Underfloor weighing	None
	1

1

KERN BFB 6T-3M



Weighing bridge with steel chequer plate weighing plate and XXL display device, verification optional

Interfaces	RS-232 (optional, factory)
IP protection - display	IP34
IP protection - load cell	IP67

Counting	
Reference quantity	10, 20, 50, 100, 200

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Plug-in power supply / adapter for countries - optional	EURO CH
Rechargeable battery optional	Rchrg. battery optional (factory)
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb

Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1550×1550×350 mm
Net weight	230 kg
Shipping method	Freight
Net weight approx.	230 kg
Gross weight approx.	280 kg
Shipping weight	279 kg

Services (optional)	
Article number for adjustment at the location of installation	961-252
Article number for conformity assessment	965-232
Article number for DAkkS calibration	963-132
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

