

# KERN BID 600K-1DM



Multi-range floor scale with the best price-to-performance ratio, verification optional



Eccentric loading at 1/3 [Max]	0,5 kg; 1 kg
Loadcell type	H8C (ZEMIC)
Load cell connection	4-wire

## Approval

CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,1 kg; 0,2 kg
Conformity assessment possible ex works	✓

## Display

Display type	LCD
Display type	LCD
Display screen size	110×35 mm
Display backlight	✓
Display digit height - smallest digit	25 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

## Construction

Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing platform (W×D×H)	1200×1500×108 mm
Material display housing	Plastics
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Dimensions weighing surface (W×D)	1200×1500 mm
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	15 m
Material load cell(s)	steel
Load cells - number	4
Levelling feet adjustable	✓
Wall mount	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min

## Category

Brand	KERN
Product category	Industrial scale
Product group	Floor scale
Product family	BID

## Measuring System

Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Number of weighing ranges	2
Weighing system	Strain gauge
Weighing capacity [Max]	300 kg; 600 kg
Readability [d]	0,1 kg; 0,2 kg
Resolution	3.000, 3.000
Linearity	± 0,3 kg; 0,6 kg
Linearisation in dots	3
Reproducibility	0,1 kg; 0,2 kg
Tare range	600 kg
Default unit	kg
Units	kg g lb oz PCS tj HJ
Units (if device is conformity assessed)	kg
Minimum weight [Min]	2 kg; 4 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	600 kg (M1)
Stabilization time	2 s
Warm-up time	10 min

# KERN BID 600K-1DM



Multi-range floor scale with the best price-to-performance ratio, verification optional

Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 standard Ethernet (optional, factory) USB (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) USB-Host/Master (optional, factory) Verification plug (optional, factory) Bluetooth BLE (v4.0) (optional, factory)
IP protection - display	IP65
IP protection - load cell	IP67
<b>Power Supply</b>	
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern

Rechargeable battery charging time	3 h
Rechargeable battery operating time - backlight on	26 h
Rechargeable battery operating time - backlight off	43 h
Battery	no battery
Battery / accumulator type	Pb

<b>Environmental conditions</b>	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

<b>Packing &amp; Shipping</b>	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1270×1560×240 mm
Net weight	150 kg
Shipping method	Freight
Net weight approx.	150 kg
Gross weight approx.	170 kg
Shipping weight	167 kg

<b>Services (optional)</b>	
Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

# KERN BID 600K-1DM



Multi-range floor scale with the best price-to-performance ratio, verification optional

## Pictograms

### STANDARD



### OPTION



### FACTORY

