

# KERN CCS 600K-2U

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



## Approval

CE mark	✓
---------	---

## Display

Display digit height	20 mm
Display backlight	✓

## Construction

Dimensions weighing platform (W×D×H)	840×1190×90 mm
Dimensions weighing surface (W×D)	840×1190 mm
Material housing	plastic
Material weighing plate	coated metal
Cable length	1,5 m
Display device cable length	5 m
Levelling feet adjustable	✓

## Functions

Number of keys for operation	20
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Conversion function	✓
Recipe/summing level	Rez A (Net total)
PLU - total	100
Sum memory function	✓
Memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard
IP protection - display	IP23
IP protection - load cell	IP65
IP protection - platform	IP65

## Counting

Smallest piece weight when piece counting - laboratory conditions	50 mg
Smallest piece weight when piece counting - normal conditions	500 mg
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)

## Category

Brand	KERN
Product category	Industrial scales
Product group	Counting scales

## Measuring System

Reference scale - Readability [d]	0,00001 kg
Quantity scale - Readability [d]	0,2 kg
Reference scale - Weighing capacity [Max]	3 kg
Quantity scale - Weighing capacity [Max]	600 kg
Eccentric loading at 1/3 [Max]	0,00005 kg
Quantity scale - Eccentric loading at 1/3 [Max]	0,4 kg
Reference scale	0,00006 kg
Reproducibility	0,00002 kg
Linearity	± 0,00005 kg
Quantity scale - Reproducibility	0,2 kg
Reference scale - Reproducibility	0,00003 kg
Reference scale - Linearity	0,0001 kg
Quantity scale - Linearity	0,4 kg
Weighing system	Strain gauge
Units	kg lb
Default unit	kg
Stabilization time	2 s
Adjustment options	Adjusting with external weight
Recommended adjusting weight	600 kg (F2)
Loadcell type	HBM PW6KRC3
Quantity scale - Item number	KFU 600V20M
Reference scale - item number	CFS 3K-5

# KERN CCS 600K-2U



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Counting resolution (laboratory conditions)	12.000.000
---	------------

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery	GAB-A04
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	70 h
Rechargeable battery operating time - backlight off	60 h

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	4 d
Shipping method	Freight
Dimensions packaging (W×D×H)	860×130×500 mm
Net weight approx.	46 kg
Gross weight approx.	50 kg

## Services (optional)

Article number for adjustment at the location of installation	abhängig von Auflösung/ Max   depends on resolution and capacity
Article number for DAkkS calibration	962-130-127
Article number for certificate of conformity (verification)	969-517

## Piktogramme

### STANDARD



### OPTION

