KERN CKE 360-3



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 180.000 points



Category				
Brand	KERN			
Product categoriy	Industrial scale			
Product group	Counting scale			
Product family	CKE			
Measuring System				
	Cingle venge helenee			
Construction type of the scale	Single-range balance			
Weighing system	Strain gauge			
Weighing capacity [Max]	360 g			
Readability [d]	0,001 g			
Resolution	360.000			
Linearity	± 0,005 g			
Reproducibility	0,001 g			
Tare range	360 g			
Default unit	g			
Units	kg g gn dwt ozt Ib oz ffa PCS			
Adjustment options	Adjusting with external weight			
Recommended adjusting weight	200 g (F1)			
Possible calibration points	100 g; 200 g; 350 g			
Stabilization time	3 s			
Warm-up time	120 min			
Eccentric loading at 1/3 [Max]	0,01 g			
Maximum creep (15 minutes)	10 mg			

Maximum creep (30 minutes)	20 mg			
Approval				
CE mark	1			
Display				
Display type	LCD			
Display screen size	89×30 mm			
Display backlight	1			
Display digit height - smallest digit	20 mm			
Display digit height	25 mm			
Languages of the user interface	Symbol language			
Construction				
Dimension housing (W×D×H)	163×245×65 mm			
Dimensions ring-shaped draught shield - inner (Ø×H)	90×40 mm			
Dimensions ring-shaped draught shield - outer (Ø×H)	106×42 mm			
Dimensions completely mounted (W×D×H)	163×245×123 mm			
Material display housing	Plastics			
Material housing	ABS plastic			
Material weighing plate	plastic			
Material platform	Stainless steel			
Material draught shield	plastic			
Dimensions weighing surface (Ø)	82 mm			
Transport safety lock - bolt torque	0,1 Nm			
Levelling feet adjustable	\checkmark			
Functions				
Number of keys for operation	7			
Auto-off interval(s) in mains power mode	off 5 min 2 min 1 min 30 min 60 min 30 sec			
Auto-off interval(s) in battery mode/rechargeable battery mode	off 5 min 2 min 1 min 30 min 60 min 30 sec			
PreTare function	1			
Tare function	manual (multi)			
Percentage determination				

KERN CKE 360-3



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 180.000 points

Counting function	1		
Tolerance weighing	1		
Tolerance weighing - type of signal	acoustically visual		
Underfloor weighing	Hook (included in delivery)		
Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)		
IP protection - complete device	-		

Counting

2 mg
20 mg
1
5, 10, 20, n (any number of pieces)
180.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz			
Input voltage device / power [Max]	5,9V, 1A			
Plug-in power supply type	Power adapter			
Supplied power supply	Power supply unit			
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH			
Plug-in power supply / adapter for countries - optional	EURO UK US CH			
Rechargeable battery optional	Rchrg. battery optional			
Rechargeable battery charging time	8 h			
Rechargeable battery operating time - backlight on	24 h			
Rechargeable battery operating time - backlight off	48 h			
Battery	4×1.5 V AA			
Battery / accumulator type	Li-Ion			
Battery connection	Battery insert			

Battery operating time	20 h			
Environmental conditions				
Humity of environment [Max]	80 %			
Ambient temperature [Min]	-10 °C			
Ambient temperature [Max]	40 °C			
Packing & Shipping				
Readability force [d] (N)	1 d			
Dimensions packaging (W×D×H)	235×365×175 mm			
Net weight	0,84 kg			
Shipping method	Parcel service			
Net weight approx.	0,85 kg			
Shipping weight	3 kg			
Services (optional)				
Article number for DAkkS	963-127			
calibration	903-127			
Article number for certificate of	969-517			
conformity (verification)	,0,01,			

Pictograms

STANDARD



OPTION

1	• 6555. •	€ →	(((.	*	五		DAkkS
ET	RS 232	USB	WLAN	BT 4.0	LAN	ACCU	+3 DAYS