

KERN CPB 15K0.2N

KERN

Professional model with counting resolution 60.000 points



Display backlight	✓
Display digit height	20 mm

Construction	
Dimensions device (W×D×H)	315×350×125 mm
Dimension housing (W×D×H)	315×350×100 mm
Dimensions completely mounted (W×D×H)	315×350×125 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	295×225 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	20
	3 min
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 30 min 15 min
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically
Recipe/summing level	Sum A
Sum memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard

Counting	
Smallest piece weight when piece counting - laboratory conditions	250 mg
Smallest piece weight when piece counting - normal conditions	2,5 g
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	60.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit

Category	
Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CPB

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,0002 kg
Resolution	75.000
Linearity	± 0,0008 kg
Reproducibility	0,0004 kg
Tare range	15 kg
Default unit	g
Units	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F2); 5 kg (F2)
Possible calibration points	15 kg
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,001 kg
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g

Approval	
CE mark	✓

Display	
Display type	LCD

KERN CPB 15K0.2N



Professional model with counting resolution 60.000 points

Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	50 h
Rechargeable battery operating time - backlight off	90 h

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	370×450×220 mm
Net weight	3,3 kg
Shipping method	Parcel service
Net weight approx.	3,4 kg
Gross weight approx.	4,4 kg
Shipping weight	7,3 kg

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

