

# KERN DBS-A01.

# KERN

Temperature calibration set consists of measuring sensor and display device



## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	290×190×50 mm
Net weight	0,235 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,6 kg

## Pictograms

### STANDARD



## Category

Brand	KERN
Product category	Balance
Product group	Temperature calibration set

## Measuring System

Temperature [Min] (°C)	-50 °C
Temperature [Max] (°C)	300 °C
Readability temperature [d] (°C)	0,1 °C
Units	°C °F

## Approval

CE mark	✓
---------	---

## Construction

Dimension (W×D×H)	115×75×18 mm
Material	plastic
Material housing	ABS plastic
Cable length	0,9 m

## Power Supply

Supplied power supply	Battery
Battery	2×1.5 V AAA
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.200 mAh
Battery voltage	3 V
Battery operating time	400 h