# KERN ECE 10K-3N

Plain, mobile, uncomplicated





| Category          |                  |
|-------------------|------------------|
| Brand             | KERN             |
| Product categoriy | Industrial scale |
| Product group     | Bench scale      |
| Product family    | ECE              |

| Measuring System               |                                |
|--------------------------------|--------------------------------|
| Construction type of the scale | Single-range balance           |
| Weighing system                | Strain gauge                   |
| Weighing capacity [Max]        | 10000 g                        |
| Readability [d]                | 5 g                            |
| Resolution                     | 2.000                          |
| Linearity                      | ± 20 g                         |
| Reproducibility                | 5 g                            |
| Default unit                   | kg                             |
| Units                          | kg                             |
| Adjustment options             | Adjusting with external weight |
| Recommended adjusting weight   | 5 kg (M3)                      |
| Possible calibration points    | 5 kg                           |
| Stabilization time             | 2 s                            |
| Warm-up time                   | 10 min                         |
| Eccentric loading at 1/3 [Max] | 15 g                           |
| Maximum creep (15 minutes)     | 10 g                           |
| Maximum creep (30 minutes)     | 20 g                           |

| Maximum creep (10 minutes) | 10 8      |   |
|----------------------------|-----------|---|
| Maximum creep (30 minutes) | 20 g      |   |
|                            |           |   |
| Approval                   |           |   |
| CE mark                    | ✓         |   |
|                            |           |   |
|                            |           |   |
| Display                    |           |   |
| Display Display type       | LCD       | ۰ |
|                            | LCD<br>no |   |
| Display type               |           |   |

| Construction                         |               |
|--------------------------------------|---------------|
| Dimension housing (W×D×H)            | 320×300×60 mm |
| Dimensions weighing platform (W×D×H) | 320×260×60 mm |
| Material display housing             | Plastics      |
| Material housing                     | plastic       |
| Material weighing plate              | plastic       |
| Dimensions weighing surface (W×D)    | 320×260 mm    |

| Functions                                |                |
|--|----------------|
| Number of keys for operation             | 2              |
| Auto-off interval(s) in mains power mode | 3 min          |
| Tare function                            | manual (multi) |
| Underfloor weighing                      | None           |
| IP protection - complete device          | +              |

| Power Supply  |                         |
|---|-------------------------|
| Input voltage power supply / power [Max]                | 220 V - 240 V AC, 50 Hz |
| Input voltage device / power [Max]                      | 9 V, 300 mA             |
| Plug-in power supply type                               | Power adapter           |
| Supplied power supply                                   | Battery                 |
| Plug-in power supply / adapter for countries - optional | EURO<br>UK<br>US<br>CH  |
| Rechargeable battery optional                           | Rchrg. battery optional |
| Rechargeable battery charging time                      | 10 h                    |
| Rechargeable battery operating time - backlight on      | 30 h                    |
| Rechargeable battery operating time - backlight off     | 30 h                    |
| Battery   | 6×1.5 V AA              |
| Battery / accumulator type                              | Alkali(-Manganese)      |
| Battery connection                                      | Pad + Spring            |
| Battery voltage   | 9 V                     |
| Battery operating time                                  | 100 h                   |

| Environmental conditions    |        |
|-----------------------------|--------|
| Humity of environment [Max] | 80 %   |
| Ambient temperature [Min]   | 5 °C   |
| Ambient temperature [Max]   | 35 °C  |
| Storage temperature [Min]   | -20 °C |
| Storage temperature [Max]   | 60 °C  |

1

## KERN ECE 10K-3N





| Packing & Shipping           |                |
|------------------------------|----------------|
| Readability force [d] (N)    | 1 d            |
| Dimensions packaging (W×D×H) | 370×330×100 mm |
| Net weight                   | 1,5 kg         |
| Shipping method              | Parcel service |
| Net weight approx.           | 1,6 kg         |
| Gross weight approx.         | 2,6 kg         |
| Shipping weight              | 2,5 kg         |

| Services (optional)   |         |
|---|---------|
| Article number for adjustment at the location of installation | 961-248 |
| Article number for DAkkS calibration                          | 963-128 |
| Article number for certificate of conformity (verification)   | 969-517 |

## Pictograms

#### **STANDARD**



### **OPTION**

