

KERN EWJ 3000-2



High-quality precision balance with automatic internal adjustment



Automatic adjustment - Standard time interval	2 h
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,05 g
Maximum creep (15 minutes)	100 mg
Maximum creep (30 minutes)	200 mg
Loadcell type	aluminium IP65 silicone-coated

Approval	
CE mark	✓

Display	
Display type	LCD
Display backlight	LED white
Display digit height	16,5 mm

Construction	
Dimension housing (W×D×H)	220×340×105 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (Ø)	135 mm
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	aluminium
Levelling feet adjustable	✓

Functions	
Number of keys for operation	7
Capacity display	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Recipe/summing level	Rez A (Net total)
Interfaces	RS-232 standard USB-Device
IP protection - display	no IP protection
IP protection - load cell	IP65

Counting	
Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	150.000

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	EWJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	3000 g
Readability [d]	0,01 g
Resolution	300.000
Linearity	± 0,05 g
Reproducibility	0,02 g
Default unit	g

Units	g
	t
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	ct
	lb
	N
	oz
	tl (Cn)
	D

Adjustment options	Internal calibration (automatic)
Recommended adjusting weight	3 kg (F1)

KERN EWJ 3000-2



High-quality precision balance with automatic internal adjustment

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V DC, 2500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	20 h
Battery / accumulator type	Pb
Battery connection	Plug-in terminals

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	390×280×270 mm
Net weight	2,886 kg
Shipping method	Parcel service
Net weight approx.	3,0 kg
Gross weight approx.	4,2 kg
Shipping weight	5,9 kg

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

