# KERN FC 500



Compact force gauge for tensile and compressive force measurements



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Digital force gauge
Product family	FC

Measuring System	
Default unit	N
Tolerance (% of [Max])	0,3%
Measuring range force [Max] (N)	500 N
Readability force [d] (N)	0,1 N
Directions of force	tension compression
Measuring head measuring frequency	1000 Hz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of individual values	500

Approval	
CE mark	<b>✓</b>
Display	
Display type	LCD
Display resolution	160×128
Display digit height	10 mm
Screen reversible	✓
Construction	
Dimension display device (W×D×H)	135×73×34 mm

135×73×34 mm

Dimension housing (W×D×H)

Dimensions completely mounted (W×D×H)	135×73×34 mm
Material display housing	Metal
Material housing	metal
Load support (tensile force)	Hook
Mounting - force application	External thread M6

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	
Hold function ✓	
Peak function   ✓	
Limit-setting function   ✓	
Memory function ✓	
Interfaces USB-Device	

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO CH
Plug-in power supply / adapter for countries - optional	UK US
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	20 h
Battery / accumulator type	NiMH
Battery connection	2-pole tub connector

Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	335×160×112 mm
Net weight	0,41 kg
Shipping method	Parcel service
Net weight approx.	0,45 kg

1

## KERN FC 500



Compact force gauge for tensile and compressive force measurements

Gross weight approx.	1,2 kg
Shipping weight	1,2 kg

Services (optional)	
Article number for DAkkS calibration (tensile force)	963-161
Article number for DAkkS calibration (compressive force)	963-261
Article number for DAkkS calibration (tensile force/compressive force)	963-361
Article number for factory calibration	961-361
Article number for factory calibration (tensile force)	961-161
Article number for factory calibration (compressive force)	961-261
Article number for factory calibration (tensile force/compressive force)	961-361

## Pictograms

#### **STANDARD**























### OPTION





