## KERN FFN 15K5IPM



All-round bench scale, protected by stainless steel and IP65 rating, verification optional



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	IP protected bench scale
Product family	FFN

Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,005 kg
Resolution	3.000
Linearity	± 0,005 kg
Reproducibility	0,005 kg
Tare range	-14,995 kg
Default unit	kg
Units	kg g
Units (if device is conformity assessed)	kg g
Minimum weight [Min]	0,1 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M3)
Possible calibration points	10 kg; 15 kg
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,005 kg

Approval	
CE mark	✓

Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,005 kg
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm

Construction	
Dimension housing (W×D×H)	243×300×127 mm
Dimensions completely mounted (W×D×H)	243×300×127 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	233×193 mm
Levelling feet adjustable	1

Functions	
Number of keys for operation	3
Auto-off interval(s) in mains power mode	3 min off 5 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 15 min
Tare function	manual (single & multi)
Underfloor weighing	None
IP protection - complete device	IP65

iP protection - complete device	1700
Power Supply	
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK

1

## KERN FFN 15K5IPM



All-round bench scale, protected by stainless steel and IP65 rating, verification optional

	US CH
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	50 h
Battery	no battery
Battery / accumulator type	Pb
Battery connection	Plug-in terminals

Environmental conditions	
Humity of environment [Min]	25 %
Humity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	310×402×205 mm
Net weight	3,85 kg
Shipping method	Parcel service
Net weight approx.	4,0 kg
Gross weight approx.	4,6 kg
Shipping weight	5,1 kg

Services (optional)	
Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms	
STANDARD	
CAL EXT UNIT IP 65 ACCU MULTI DMS 1 DAY	
OPTION	
DAkkS +3 DAYS	



**FACTORY**