

# KERN FH 20K



Universal digital force gauge for tensile and compressive force measurements with external load cell



## Construction

Dimension display device (W×D×H)	230×66×36 mm
Dimension housing (W×D×H)	230×65×36 mm
Dimensions completely mounted (W×D×H)	230×65×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Rod end
Mounting - force application	Threaded hole M12
Mounting - force dissipation	Threaded hole M12

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min
Hold function	✓
Peak function	✓
Statistic function	✓
Limit-setting function	✓
Memory function	✓
Interfaces	RS-232 standard

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO CH
Plug-in power supply / adapter for countries - optional	UK US
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NiMH

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
---------------------------	-----

## Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (external measuring cell)
Product family	FH-M

## Measuring System

Default unit	kN
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	20 kN
Readability force [d] (N)	10 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display digit height	10 mm
Screen reversible	✓

# KERN FH 20K



Universal digital force gauge for tensile and compressive force measurements with external load cell

Dimensions packaging (W×D×H)	325×185×165 mm
Net weight	1,79 kg
Shipping method	Parcel service
Net weight approx.	1,8 kg
Gross weight approx.	3,0 kg
Shipping weight	2,95 kg

## Services (optional)

Article number for factory calibration (tensile force)	961-164
Article number for factory calibration (compressive force)	961-264
Article number for factory calibration (tensile force/ compressive force)	961-364

## Pictograms

### STANDARD



### OPTION

