KERN FH 2KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Digital force gauge (external measuring cell)
Product family	FH-M
Measuring System	
Default unit	kN

	KIN .
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	2 kN
Readability force [d] (N)	1 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

Approval

CE mark

Display

Dispidy		
Display type	LCD	
Display digit height	10 mm	
Screen reversible	\checkmark	

1

Construction	
Dimension display device (W×D×H)	230×66×36 mm
Dimension housing (W×D×H)	230×66×36 mm
Dimensions completely mounted (W×D×H)	230×66×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Rod end
Mounting - force application	Threaded hole M12
Mounting - force dissipation	Threaded hole M12
Functions	
Auto-off interval(s) in battery	1 - 60 min

mode/rechargeable battery mode	1 - 60 min
Peak function	1
Statistic function	1
Limit-setting function	1
Memory function	1
Interfaces	RS-232 standard
Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	UK
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NIMH
Environmental conditions	
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	325×185×165 mm
Net weight	1,556 kg
	1,000 Kg

1,6 kg

Net weight approx.

KERN FH 2KUK



Universal digital force gauge for tensile and compressive force measurements with external load cell, with plug-in power supply for UK

Gross weight approx. Shipping weight	2,8 kg 2,734 kg
Services (optional)	
Article number for DAkkS calibration (tensile force)	963-162
Article number for DAkkS calibration (compressive force)	963-262
Article number for DAkkS calibration (tensile force/ compressive force)	963-362
Article number for factory calibration (tensile force)	961-162
Article number for factory calibration (compressive force)	961-262
Article number for factory calibration (tensile force/ compressive force)	961-362

Pictograms

STANDARD

