

KERN FH 2UK



Universal digital force gauge for tensile and compressive force measurements with integrated load cell, with plug-in power supply for UK



Construction

Dimension display device (W×D×H)	230×66×36 mm
Dimension housing (W×D×H)	230×66×36 mm
Dimensions completely mounted (W×D×H)	230×66×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Hook

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min
Peak function	✓
Statistic function	✓
Limit-setting function	✓
Memory function	✓
Interfaces	RS-232 standard

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	UK
	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NiMH

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	312×170×60 mm
Net weight	0,62 kg

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (internal measuring cell)
Product family	FH-S

Measuring System

Default unit	N
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	2 N
Readability force [d] (N)	0,001 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Number of platforms / channels	1
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display digit height	10 mm
Screen reversible	✓

KERN FH 2UK



Universal digital force gauge for tensile and compressive force measurements with integrated load cell, with plug-in power supply for UK

Shipping method	Parcel service
Net weight approx.	0,65 kg
Gross weight approx.	1,4 kg
Shipping weight	1,224 kg

Services (optional)

Article number for factory calibration (tensile force)	961-161
Article number for factory calibration (compressive force)	961-261
Article number for factory calibration (tensile force/ compressive force)	961-361

Pictograms

STANDARD



OPTION

