KERN FOB 10K-3LM



Compact stainless steel bench scale with special checkweighing display for even more efficient working, verification optional



| Category | |
|-------------------|-----------------------------|
| Brand | KERN |
| Product categoriy | Industrial scale |
| Product group | Stainless steel bench scale |
| Product family | FOB-LM |

| Measuring System | |
|--|--------------------------------|
| Conformity assessment possible | ✓ |
| Construction type of the scale | Single-range balance |
| Number of weighing ranges | 1 |
| Weighing system | Strain gauge |
| Weighing capacity [Max] | 15 kg |
| Readability [d] | 0,005 kg |
| Resolution | 3.000 |
| Linearity | ± 0,01 kg |
| Reproducibility | 0,005 kg |
| Default unit | kg |
| Units | kg |
| Units (if device is conformity assessed) | kg |
| Minimum weight [Min] | 0,1 kg |
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 10 kg (M1) |
| Possible calibration points | 10 kg |
| Stabilization time | 2 s |
| Warm-up time | 10 min |
| Eccentric loading at 1/3 [Max] | 0,015 kg |

| Approval | |
|----------|---|
| CE mark | ✓ |

| Pattern approval for conformity assessment | ✓ |
|--|----------|
| Accuracy classe | III |
| Verification scale interval [e] | 0,005 kg |
| Conformity assessment possible ex works | ✓ |

| Display | |
|----------------------|-------|
| Display type | LCD |
| Display backlight | ✓ |
| Display digit height | 25 mm |

| Construction | |
|-----------------------------|-----------------|
| Dimension housing (W×D×H) | 256×285×100 mm |
| Material housing | stainless steel |
| Material weighing plate | stainless steel |
| Dimensions weighing surface | 248×198 mm |

| Functions |
|--|
| Auto-off interval(s) in battery mode/rechargeable battery mode 2 min |
| Tare function manual (multi) |
| Tolerance weighing |
| Tolerance weighing - type of signal visual |
| IP protection - complete device IP67 |

| Power Supply | |
|---|--------------------|
| Input voltage power supply / power [Max] | 230 V AC, 50 Hz |
| Input voltage device / power [Max] | 12 V, 500 mA |
| Plug-in power supply type | Power adapter |
| Supplied power supply | Power supply unit |
| Plug-in power supply / adapter for countries - included with the delivery | EURO |
| Plug-in power supply / adapter for countries - optional | EURO CH |
| Battery | 4×1.5 V AA |
| Battery / accumulator type | Alkali(-Manganese) |
| Battery connection | Pad + Spring |
| Battery operating time | 48 h |
| Battery operating time - backlight on | 48 h |
| Battery operating time - backlight off | 66 h |

1

KERN FOB 10K-3LM



Compact stainless steel bench scale with special checkweighing display for even more efficient working, verification optional

| Environmental conditions | |
|-----------------------------|-------|
| Humity of environment [Min] | 25 % |
| Humity of environment [Max] | 95 % |
| Ambient temperature [Min] | 0 °C |
| Ambient temperature [Max] | 40 °C |

| Packing & Shipping | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 420×305×180 mm |
| Net weight | 3,8 kg |
| Shipping method | Parcel service |
| Net weight approx. | 3,8 kg |
| Gross weight approx. | 4,8 kg |
| Shipping weight | 4,7 kg |

| Services (optional) | |
|---|---------|
| Article number for adjustment at the location of installation | 961-248 |
| Article number for conformity assessment | 965-228 |
| Article number for DAkkS calibration | 963-128 |
| Article number for certificate of conformity (verification) | 969-517 |

Pictograms

STANDARD















OPTION



FACTORY

