

KERN FOB-A02

Power adapter (EU/UK/US)

KERN



Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Cable length	1,5 m
--------------	-------

Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply / adapter for countries - included with the delivery	UK

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	93×85×62 mm
Net weight	0,35 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,40 kg
Shipping weight	0,38 kg