KERN FOB-A10

Power adapter (EU/UK/US)





Pictograms

STANDARD



Category	
Brand	KERN
Product categoriy	Balance
Product group	Power adapter
Measuring System	
Linearity	±
Approval	
CE mark	1
Construction	
Cable length	1,5 m
Power Supply	
Input voltage power supply / power [Max]	230 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 100 mA
Plug-in power supply / adapter for countries - included with the delivery	UK
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	73×89×53 mm
Net weight	0,24 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,30 kg
Shipping weight	0,255 kg