

# KERN GAB 30K0.2N

Checkweighing and portioning scale

# KERN



Display backlight	✓
Display digit height	24 mm

## Construction

Dimension housing (W×D×H)	315×350×100 mm
Dimensions completely mounted (W×D×H)	315×350×125 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	295×225 mm
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Recipe/summing level	Sum A
Sum memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard

## Counting

Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	150.000

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit

## Category

Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	GAB

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg
Readability [d]	0,0002 kg
Resolution	150.000
Linearity	± 0,0006 kg
Reproducibility	0,0002 kg
Tare range	-30 kg
Default unit	kg

Units	kg g t lb oz
-------	--------------------------

Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (F1); 10 kg (F1)
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,001 kg
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
--------------	-----

# KERN GAB 30K0.2N



Checkweighing and portioning scale

Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	40 h
Rechargeable battery operating time - backlight off	90 h

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	450×375×210 mm
Net weight	3 kg
Shipping method	Parcel service
Net weight approx.	3,0 kg
Gross weight approx.	4,4 kg
Shipping weight	7,1 kg

## Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

