
KERN **HBA 100-0**







Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Analogue Shore hardness tester
Product family	НВ

Measuring System	
Units	НА
Tolerance (% of [Max])	3%
Test force Hardness measurement	10 N
Hardness scales	Shore A
Measuring probe diameter	18 mm
Test object thickness [Min]	6 mm
Readability hardness [d] (Shore)	1
Measuring range Shore	100

Construction	
Dimension (W×D×H)	115×60×25 mm
Dimension housing (W×D×H)	115×60×25 mm
Dimensions completely mounted (W×D×H)	115×60×25 mm
Material housing	metal
Scale - Display type	Analogue

Environmental conditions	
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	147×98×54 mm
Net weight	0,15 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,50 kg
Shipping weight	0,46 kg

Pictograms

STANDARD



