KERN HCN 200K500IP



Robust, compact hanging scale with high level of protection against dust and water spray



| Category | |
|-------------------|------------------|
| Brand | KERN |
| Product categoriy | Industrial scale |
| Product group | Hanging scale |
| Product family | HCN |

| Measuring System | |
|--|--------------------------------|
| Construction type of the scale | Single-range balance |
| Weighing system | Strain gauge |
| Weighing capacity [Max] | 200 kg |
| Readability [d] | 0,5 kg |
| Resolution | 400 |
| Linearity | ± 1 kg |
| Reproducibility | 0,5 kg |
| Default unit | kg |
| Units | kg Ib N |
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 100 kg (M3) |
| Stabilization time | 2 s |
| Warm-up time | 10 min |
| Eccentric/Off-centre loading is not possible | / |
| Maximum creep (15 minutes) | 1 kg |
| Maximum creep (30 minutes) | 2 kg |
| Tolerance (% of [Max]) | 0,5% |
| Internal measuring frequency | 5 Hz |

| Approval | |
|----------|---|
| CE mark | ✓ |

| Display | |
|---------------------------|------------------|
| Display type | LCD |
| Display digit height | 12 mm |
| Construction | |
| Dimension housing (W×D×H) | 96×48×179 mm |
| Material housing | stainless steel |
| Material load hook | stainless steel |
| Material load cell(s) | Stainless steels |

| Functions | |
|--|----------------|
| Number of keys for operation | 3 |
| Auto-off interval(s) in mains power mode | 3 min |
| Auto-off interval(s) in battery mode/rechargeable battery mode | 3 min |
| Tare function | manual (multi) |
| Hold function | ✓ |
| Underfloor weighing | None |
| IP protection - complete device | IP65 |

| Power Supply | |
|----------------------------|--------------------|
| Supplied power supply | Battery |
| Battery | 2×1.5 V AA |
| Battery / accumulator type | Alkali(-Manganese) |
| Battery voltage | 3 V |
| Battery operating time | 200 h |

| Environmental conditions | |
|-----------------------------|-------|
| Humity of environment [Max] | 80 % |
| Ambient temperature [Min] | 5 °C |
| Ambient temperature [Max] | 35 °C |
| Storage temperature [Max] | 60 °C |

| Packing & Shipping | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 150×220×73 mm |
| Net weight | 0,5 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,50 kg |
| Gross weight approx. | 1,2 kg |
| Shipping weight | 1,1 kg |

| Services (optional) | |
|---|---------|
| Article number for adjustment at the location of installation | 961-249 |

1

KERN HCN 200K500IP



Robust, compact hanging scale with high level of protection against dust and water spray

Article number for DAkkS calibration

963-129H

Article number for certificate of conformity (verification)

969-517

Pictograms

STANDARD













OPTION

