KERN HDB 10K10N

Practical hanging scale for rapid, mobile weighing





Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Hanging scale
Product family	HDB

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10 kg
Readability [d]	0,01 kg
Resolution	1.000
Linearity	± 0,03 kg
Reproducibility	0,01 kg
Default unit	kg
Units	kg Ib N
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric/Off-centre loading is not possible	/
Maximum creep (15 minutes)	20 g
Maximum creep (30 minutes)	40 g
Tolerance (% of [Max])	0,5%
Internal measuring frequency	5 Hz

Approval	
CE mark	✓

Display	
Display type	LCD
Display backlight	no
Display digit height	12 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	72×25×105 mm
Dimensions completely mounted (W×D×H)	72×25×188 mm
Material housing	plastic
Material load hook	steel

Functions	
Number of keys for operation	3
Tare function	manual (multi)
Hold function	✓
Function for averaging under unstable weighing conditions	1
Peak function	✓
Underfloor weighing	None

Power Supply	
Supplied power supply	Battery
Battery	2×1.5 V AAA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	1.200 mAh
Battery voltage	1,5 V
Battery operating time	180 h

Environmental conditions	
Humity of environment [Max]	90 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	225×150×70 mm
Net weight	0,192 kg
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,45 kg
Shipping weight	0,5 kg

1

KERN HDB 10K10N





Services (optional)

Article number for adjustment at 961-248 the location of installation

Article number for DAkkS 963-128H calibration

Article number for certificate of 969-517 conformity (verification)

Pictograms

STANDARD











OPTION

