KERN **HK-DB**



Premium Leeb hardness tester - also with hardness comparison block included



Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Leeb hardness tester
Product family	HK

Measuring System	
Units	HL HV HB HRB HRC
Tolerance (% of [Max])	1%
Hardness scales	HLD
Readability [d] hardness (Hlx)	1
Leeb Hardness Tester sensor type	D
Measuring range [Min] (HLx)	170
Measuring range [Max] (HLx)	960
Test block inclusive	✓
Measuring probe diameter	2 cm
Measuring probe length	14,6 cm
Test object thickness [Min]	2 mm
Test object minimum weight [Min]	2 kg

Approval		
CE mark	✓	

Display	
Display type	LCD graphic
Display digit height	11 mm

Construction	
Dimension (W×D×H)	132×82×31 mm
Dimension housing (W×D×H)	132×82×31 mm
Dimensions completely mounted (W×D×H)	132×82×31 mm
Material housing	cast aluminium
Scale - Display type	Digital

Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	0,5 - 60 min
360° measurement possible	✓
Statistic function	✓
Memory function	✓
Interfaces	USB-Device

Power Supply	
Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery operating time	200 h

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	368×215×85 mm
Net weight	0,425 kg
Shipping method	Parcel service
Net weight approx.	0,45 kg
Gross weight approx.	4,2 kg
Shipping weight	4,2 kg

Services (optional)	
Article number for factory calibration	961-131

1

KERN HK-DB



Premium Leeb hardness tester - also with hardness comparison block included

Pictograms

STANDARD













OPTION



