KERN HK-D



Premium Leeb hardness tester - also with hardness comparison block included



Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	Leeb hardness tester
Product family	НК
Measuring System	
Units	HL HV HB HRB HRC
Tolerance (% of [Max])	1%
Hardness scales	HLD
Readability [d] hardness (Hlx)	1
Leeb Hardness Tester sensor type	D
Measuring range [Min] (HLx)	170
Measuring range [Max] (HLx)	960
Measuring probe diameter	2 cm
Measuring probe length	14,6 cm
Test object thickness [Min]	2 mm
Test object minimum weight [Min]	2 kg
Approval	
CE mark	✓
Display	
Display type	LCD graphic
Display digit height	11 mm

brana	oduter
Product categoriy	Hardness testing
Product group	Leeb hardness tester
Product family	НК
Measuring System	
	HL
	HV
Units	HB
	HRB
	HRC
Tolerance (% of [Max])	1%
Hardness scales	HLD
Readability [d] hardness (Hlx)	1
Leeb Hardness Tester sensor type	D
Measuring range [Min] (HLx)	170
Measuring range [Max] (HLx)	960
Measuring probe diameter	2 cm
Measuring probe length	14,6 cm
Test object thickness [Min]	2 mm
Test object minimum weight [Min]	2 kg
A	
Approval	
CE mark	\checkmark
Dioplay	
Display	
Display type	LCD graphic
Display digit height	11 mm

Construction

Dimension (W×D×H)

132×82×31 mm

Dimension housing (W×D×H)	132×82×31 mm
Dimensions completely mounted (W×D×H)	132×82×31 mm
Material housing	cast aluminium
Scale - Display type	Digital
	Ũ
Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	0,5 - 60 min
360° measurement possible	✓
Statistic function	✓
Limit-setting function	1
Memory function	✓
Interfaces	USB-Device
Power Supply	
Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery operating time	200 h
Environmental conditions	
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	370×220×87 mm
Net weight	0,45 kg
Shipping method	Parcel service
Net weight approx.	0,45 kg
Gross weight approx.	1,6 kg
Shipping weight	1,54 kg
Services (optional)	
Article number for factory	
-	0(1 101
calibration	961-131

KERN **HK-D**



Premium Leeb hardness tester - also with hardness comparison block included

Pictograms

STANDARD



OPTION

