KERN HO 10K



Premium UCI hardness testing device for Rockwell, Brinell and Vickers



Category	
Brand	Sauter
Product categoriy	Hardness testing
Product group	UCI hardness tester
Product family	НО
Measuring System	
Units	HL HV HB HRB HRC MPa HRA
Test force Hardness measurement	100 N
Hardness scales	HV 10
Measuring range Rockwell - scale A	61-85,6HRA
Measuring range Rockwell - scale B	41-100HRB
Measuring range Rockwell - scale C	20,3-68HRC
Measuring range Vickers	80-1599HV
Measuring range Brinell	79-618HB
Measuring range tensile strength	255-2180MPa
Test block inclusive	\checkmark
Measuring probe diameter	18 mm
Measuring probe length	15,5 cm
Test object thickness [Min]	2 mm
Test object minimum weight [Min]	300 g

Approval

CE mark

1
-

Display	
Display type	LCD graphic
Construction	
Dimension (W×D×H)	28×83×160 mm
Dimension housing (W×D×H)	28×83×160 mm
Dimensions completely mounted (W×D×H)	28×83×160 mm
Material housing	metal, lacquered
Type of drive	manual
Scale - Display type	Digital
Functions	
Auto-off interval(s) in battery mode/rechargeable battery mode	30 min
360° measurement possible	✓
Statistic function	1
Limit-setting function	1
Memory function	1
Memory - number of results	1.000
Interfaces	USB-Device
Power Supply	
Input voltage power supply / power [Max]	110 - 240 V
Input voltage device / power [Max]	5 V, 2 A
Plug-in power supply type	USB including power supply
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO AUS UK US
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	6 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	Li-Ion
Battery connection	Connector pin
Dattery connection	

KERN HO 10K



Premium UCI hardness testing device for Rockwell, Brinell and Vickers

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	395×325×150 mm
Net weight	0,869 kg
Shipping method	Parcel service
Net weight approx.	0,90 kg
Gross weight approx.	4,4 kg
Shipping weight	4,38 kg

Services (optional)	
Article number for factory calibration	961-270

Pictograms

STANDARD





OPTION

