

KERN IFS 60K0.5DL

Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 60.000 points



Display backlight	✓
Display digit height - smallest digit	13,5 mm
Display digit height	16,5 mm

Construction

Dimension display device (W×D×H)	260×150×65 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Dimensions completely mounted (W×D×H)	500×400×120 mm
Material display housing	Plastics
Material weighing plate	stainless steel
Material platform	mild steel
Dimensions weighing surface (W×D)	500×400 mm
Display device cable length	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓
Stand height	600 mm
Stand inclinable	✓

Functions

Number of keys for operation	21
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Peak function	✓
Recipe/summing level	Sum A
PLU - total	100
Sum memory function	✓
Memory function	✓
Interfaces	RS-232 standard
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	IP65
IP protection - platform	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	1 g
---	-----

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	IFS

Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	0,0005 kg; 0,001 kg
Resolution	60.000, 60.000
Linearity	± 0,003 kg; 0,006 kg
Reproducibility	0,0005 kg; 0,001 kg
Tare range	-60 kg
Default unit	kg
Units	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (F2)
Stabilization time	2 s
Warm-up time	120 min; 120 min
Eccentric loading at 1/3 [Max]	0,004 kg; 0,008 kg
Maximum creep (15 minutes)	10 g
Maximum creep (30 minutes)	20 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	4-wire

Approval

CE mark	✓
---------	---

Display

Display type	LCD
--------------	-----

KERN IFS 60K0.5DL



Industrial counting scale with convenient decimal keypad for easy data entry,
counting resolution 60.000 points

Smallest piece weight when piece counting - normal conditions	10 g
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	60.000

Power Supply

Input voltage power supply / power [Max]	100 - 240 V~ 50/60 Hz 190 mA
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional (factory)
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	18 h
Battery / accumulator type	Pb

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	930×545×210 mm
Net weight	12 kg
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	15 kg
Shipping weight	21,3 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

