


KERN IOC 10K-4L



High-resolution allround platform scale with a wide range of communication options



Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IOC

Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6 kg; 15 kg
Readability [d]	0,0002 kg; 0,0005 kg
Resolution	30.000, 30.000
Linearity	± 0,0006 kg; 0,0015 kg
Linearisation in dots	3
Reproducibility	0,0002 kg; 0,0005 kg
Default unit	kg

Units	kg
	g
	lb
	oz
	PCS
	tj HJ

Minimum weight [Min]	0,04 kg; 0,1 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Stabilization time	2 s
Warm-up time	120 min; 120 min
Eccentric loading at 1/3 [Max]	0,01 kg; 0,025 kg
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	4-wire

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display type	LCD
Display screen size	110×35 mm
Display backlight	✓
Display digit height - smallest digit	25 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction

Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing platform (W×D×H)	400×300×110 mm
Material display housing	Plastics
Material weighing plate	stainless steel
Material platform	mild steel
Dimensions weighing surface (W×D)	400×300 mm
Display device cable length	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓
Stand inclinable	✓

Functions

Number of keys for operation	7	
Auto-off interval(s) in mains power mode	3 min	
	off	
	5 min	
Auto-off interval(s) in battery mode/rechargeable battery mode	30 min	
	15 min	
	3 min	
Auto-off interval(s) in battery mode/rechargeable battery mode	off	
	5 min	
	30 min	
Auto-off interval(s) in battery mode/rechargeable battery mode	15 min	
	PreTare function	✓
	Tare function	manual (multi)
Percentage determination	✓	
Counting function	✓	
Tolerance weighing	✓	
Tolerance weighing - type of signal	acoustically visual	

KERN IOC 10K-4L



High-resolution allround platform scale with a wide range of communication options

Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 standard
	Ethernet (optional, factory)
	USB (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	USB-Host/Master (optional, factory)
	Verification plug (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
IP protection - complete device	IP65
IP protection - display	IP65
IP protection - load cell	IP65
IP protection - platform	IP65

Counting	
Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	30.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	3 h

Rechargeable battery operating time - backlight on	26 h
Rechargeable battery operating time - backlight off	43 h
Battery	no battery
Battery / accumulator type	Pb
Battery operating time	100 h

Environmental conditions	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	815×360×185 mm
Net weight	7,28 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	9 kg
Shipping weight	10,9 kg

Services (optional)	
Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517


KERN IOC 10K-4L



High-resolution allround platform scale with a wide range of communication options

Pictograms

STANDARD



OPTION



FACTORY

