

KERN KDE-T

Display device



Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Time display	✓
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Interfaces	RS-232 standard

Counting

Reference quantity	5, 10, 20, 25, 50
--------------------	-------------------

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

Rechargeable battery optional	Rchrg. battery optional - intern
-------------------------------	----------------------------------

Rechargeable battery charging time	10 h
------------------------------------	------

Rechargeable battery operating time - backlight on	10 h
--	------

Rechargeable battery operating time - backlight off	15 h
---	------

Battery	9 V block
---------	-----------

Battery operating time	24 h
------------------------	------

Environmental conditions

Humidity of environment [Max]	80 %
-------------------------------	------

Ambient temperature [Min]	5 °C
---------------------------	------

Ambient temperature [Max]	35 °C
---------------------------	-------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Category

Brand	KERN
Product category	Spare part
Product group	Spare part

Measuring System

Number of weighing ranges	2
Terminal resolution (not verifiable)	20.000
Linearisation in dots	4
Default unit	kg
Units	kg g lb oz
Adjustment options	Adjusting with external weight

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	225×110×45 mm
Material display housing	Plastics

Functions

Auto-off interval(s) in mains power mode	off
--	-----

KERN KDE-T



Display device

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	205×270×70 mm
Net weight	0,7 kg
Shipping method	Parcel service
Net weight approx.	0,70 kg
Gross weight approx.	1,00 kg
Shipping weight	1 kg

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------

Pictograms