

KERN KDE-TH

Display device



Functions

Auto-off interval(s) in mains power mode	selectable
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Time display	✓
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Interfaces	RS-232 standard
IP protection - complete device	IP65

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	15 V, 600 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	15 h
Battery	9 V block
Battery operating time	24 h

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Category

Brand	KERN
Product category	Spare part
Product group	Spare part

Measuring System

Number of weighing ranges	2
Terminal resolution (not verifiable)	35.000
Linearisation in dots	3
Default unit	kg
Units	kg g lb oz ffa
Adjustment options	Adjusting with external weight

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	225×110×45 mm
Material display housing	Plastics
Display device cable length	1,5 m

KERN KDE-TH



Display device

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	260×170×150 mm
Net weight	1 kg
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,00 kg
Shipping weight	1,3 kg

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------

Pictograms