

KERN KFU 1500V30M

U-Weighing bridge, Load range: stainless steel

KERN



Category

Brand	KERN
Product category	Component
Product group	Weighing bridge
Product family	KFU-V20

Measuring System

Weighing capacity [Max]	1500 kg
Readability [d]	500 g
Minimum weight [Min]	10 kg

Approval

Verification scale interval [e]	500 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	840×1300×90 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Cable length	5 m
Allowed cable length display device [Max]	5 m
Load cells - number	4
Levelling feet adjustable	✓

Functions

IP protection - complete device	IP68
---------------------------------	------

Packing & Shipping

Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1380×850×310 mm

Net weight	52 kg
Shipping method	Freight
Net weight approx.	55 kg
Gross weight approx.	85 kg
Shipping weight	84 kg

Services (optional)

Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130

Pictograms

STANDARD



FACTORY

