KERN KFU 600V20M

U-Weighing bridge, Load range: painted steel





Category	
Brand	KERN
Product categoriy	Component
Product group	Weighing bridge
Product family	KFU-V20

Measuring System		
Weighing capacity [Max]	600 kg	
Readability [d]	200 g	
Minimum weight [Min]	4 kg	

Approval	
Verification scale interval [e]	200 g
Conformity assessment possible ex works	✓

Construction	
Dimensions weighing platform (W×D×H)	840×1300×90 mm
Material weighing plate	steel, lacquered
Cable length	5 m
Allowed cable length display device [Max]	5 m
Material load cell(s)	alloyed steel
Load cells - number	4
Levelling feet adjustable	✓

Functions	
IP protection - complete device	IP67 (load cell)
IP protection - load cell	IP67

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1380×850×310 mm
Net weight	52 kg
Shipping method	Freight

Net weight approx.	55 kg
Gross weight approx.	85 kg
Shipping weight	84 kg

Services (optional)		
Article number for conformity assessment	965-230	
Article number for DAkkS calibration	963-130	

Pictograms

STANDARD



FACTORY



1