

KERN KXP 30V20M



Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



IP protection - load cell IP65

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	500×410×225 mm
Net weight	7,8 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	9 kg
Shipping weight	9,2 kg

Services (optional)

Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128

Pictograms

STANDARD



FACTORY



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KXP

Measuring System

Weighing capacity [Max]	15 kg; 30 kg
Readability [d]	1 g
Minimum weight [Min]	100 g; 200 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

Approval

Verification scale interval [e]	5 g; 10 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	400×300×90 mm
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	400×300 mm
Cable length	3 m
Allowed cable length display device [Max]	10 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓

Functions

IP protection - complete device	IP65 (load cell)
---------------------------------	------------------